

Fluke Networks Pro3000™ Tone Generator and Probe Kit



Key features

- Send tone signal up to 10 miles (16 km) on most cables
- Analog tone generator with bed-of-nails clips, unfiltered probe
- SmartTone™ provides 5 distinct tones for exact pair identification
- Continuity testing and line polarity confirmation
- Ergonomic sleek design, 3.5 mm headphone jack

Product overview: Fluke Networks Pro3000™ Tone Generator and Probe Kit

Pro3000™ analog tone generator and probe kit uses the SmartTone™ technology, with five different tones for exact pair identification, and provides clear and precise tracing of communication cabling. Simply short the selected pair at the near or far end to change the cadence of the tone generated.

Specifications: Fluke Networks Pro3000™ Tone Generator and Probe Kit

Pro3000 Analog Toner Specifications

User interface	Slide switch selects Continuity or Tone Mode Push button switch selects SOLID, ALT or OFF Tone mode LED Continuity/Polarity LED
Solid Frequency	1000 Hz nominal
Alternating Frequency	1000/1500 Hz nominal
Over Voltage Protection	60 Vdc in Toner/Polarity Mode
Output Power in Tone Mode	8 dbm into 600 ohms
Output Voltage Level in Continuity Mode	8 Vdc with fresh battery
Battery	9V alkaline
Temperature	Operating: -20° C to 60° C, Storage: -40° C to 70° C
Case dimensions	2.7 in. x 2.4 in. x 1.4 in. (6.9 cm x 6.1 cm x 3.6 cm)

Pro3000 Analog Probe Specifications

User interface	ON/OFF push button Volume dial Replaceable tip 3.5 mm earphone jack
Battery	9V alkaline
Temperature	Operating: -20° C to 60° C, Storage: -40° C to 70° C
Case dimensions	9.8 in. x 1.6 in. x 1.3 in. (24.9 cm x 4.1 cm x 3.3 cm)

Fluke. *Keeping your world up and running.®*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (905) 890-7600

From other countries +1 (425) 446-5500

Representative office of Fluke South East Asia Pte Ltd

C/O Danaher Vietnam

Green Power Tower, 11th Floor Unit 2

35 Ton Duch Thang Street, District 1

Ho Chi Minh City

Vietnam

Tel: +84-8-2220-5371 (ext 103)

Email: info.asean@fluke.com

www.fluke.com/vn-vi

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.