

TECHNICAL DATA

Fluke i17XX-flex1500 iFlex® Current Clamp



Product overview: Fluke i17XX-flex1500 iFlex® Current Clamp

The Fluke 17XX 12 inch iFlex flexible current probes measure to 1500A AC while providing the ultimate measurement flexibility. The iFlex probes connect directly to the 173X Energy or Power Logger, displaying current measurements without error prone scaling factors. The 1.8 m (6 ft) cord allows separation between the measurement location and the energy logger making it easier to view the display. Fluke 17XX iFlex cables are available in 12, 24, and 36 inch models.

Ordering information



i17XX-flex1500

1500A 12 inch iFlex® Current Clamps

Fluke. *Keeping your world up and running.®*

Fluke Europe B.V.

P.O. Box 1186
5602 BD Eindhoven
The Netherlands
www.fluke.com/en

©2022 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
01/2022

For more information call:

In Middle East/Africa
+31 (0)40 267 5100

**Modification of this document is not permitted
without written permission from Fluke Corporation.**