

TECHNICAL DATA

# Fluke AC89 Heavy Duty Insulation Piercing Test Clip



## Key features

- Single probe pierces 0.25 to 1.5 mm insulated wire
- Extremely small piercing point allows for maximum integrity of insulation
- 30Vrms, 42.4Vpk, 60Vdc, 10A
- One year warranty

## Ordering information



**Fluke AC89**

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Europe B.V.**

P.O. Box 1186  
5602 BD Eindhoven  
The Netherlands  
[www.fluke.com/en](http://www.fluke.com/en)

©2021 Fluke Corporation. All rights reserved.  
Data subject to alteration without notice.  
10/2021

**For more information call:**

In Middle East/Africa  
+31 (0)40 267 5100

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**