

TECHNICAL DATA

## Fluke TL76 2mm/4mm Test Lead Set



### Key features

- Removable, insulated IC caps allow probing on closely spaced leads and compliance with GS38
- CAT II 1000 V, 10 A rating
- CAT III 1000 V, CAT IV 600V only with protective cap
- One year warranty

### Product overview: Fluke TL76 2mm/4mm Test Lead Set

One pair (red, black) silicone test leads with right angle shrouded 4 mm (0.16 in) banana plugs.

## Ordering information



### Fluke TL76

- One pair (red, black) 1.5 meter long silicone test leads with right angle shrouded banana plug
- Lantern tip (removable) for use with European wall sockets (4 mm Ø)
- Lantern tip can be removed for easy access to terminal blocks (2 mm Ø)

**Fluke.** *Keeping your world up and running.®*

**Fluke Europe B.V.**

P.O. Box 1186  
5602 BD Eindhoven  
The Netherlands  
[www.fluke.com/en](http://www.fluke.com/en)

©2021 Fluke Corporation. All rights reserved.  
Data subject to alteration without notice.  
11/2021

**For more information call:**

In Middle East/Africa  
+31 (0)40 267 5100

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**