


TECHNICAL DATA

Fluke TL950 Mini-Pincer Test Leads



Key features

- 1 pair (red, black) of test leads with multi-stacking 4 mm banana plugs and mini-pincers
- Mini-pincers open to 2.3 mm
- 90 cm long PVC insulated leads
- 30 V rms or 60 V DC, 3 A
- One year warranty

Ordering information



Fluke TL950

Fluke. *Keeping your world up and running.®*

Fluke Europe B.V.

P.O. Box 1186
5602 BD Eindhoven
The Netherlands
www.fluke.com/en

©2021 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
11/2021

For more information call:

In Middle East/Africa
+31 (0)40 267 5100

**Modification of this document is not permitted
without written permission from Fluke Corporation.**