

TECHNICAL DATA

# Fluke 87V/E2 Industrial Electrician Combo Kit



## Key features

All functionality of the 87V Industrial Digital Multimeter, plus:

- Fully insulated 3 mm exposed metal test probes for electricians working in high energy environments
- C35 Soft Carrying Case holds meter, test leads and other accessories
- TPAK magnetic hanging strap lets you attach the meter to any ferrous surface, such as cabinets and iron pipes.

## Product overview: Fluke 87V/E2 Industrial Electrician Combo Kit

Ideal for electricians, this combo kit is built around the Fluke 87V, the most widely used industrial digital multimeter in the world and includes essential accessories to make you even more productive. This kit offers 15% savings compared with the individual price of all the accessories. Plus you'll be working with the most trusted tools in the world.

Assembled in the USA. Lifetime warranty.

The Fluke 87V/E2 Industrial Electrician Combo Kit is designed and assembled in the USA. The 87V multimeter is backed by a limited lifetime warranty, so you can rely on your DMM every time you take it out of your tool box.

### Solve the difficult problems

Working on VSDs/VFDs: Take accurate voltage, current and frequency measurements on the output side of the drive at either the drive itself or at the motor terminals.

Industrial troubleshooting: Get the resolution and accuracy you need to solve more problems on motor drives, in-plant automation, power distribution, and electromechanical equipment.

Checking power quality: Capture glitches and spikes as short as 250  $\mu$ s. Identify irregular signals.

### Advanced measurement functions

- True-rms ac measurements
- 0.05% dc accuracy
- 6,000 counts, 3-3/4 digit resolution, or 20,000 counts, 4-1/2 digit—resolution
- 10 A ac or dc (with test leads and current jacks) with 0.1  $\mu$ A resolution
- Temperature measurements up to 1090 °C with included thermocouple probe
- Provides 10,000  $\mu$ F capacitance range for components and motor caps
- Provides peak capture and Min/Max/Avg recording to capture intermittent as short as 250  $\mu$ S
- Easy access door for fast battery changes without breaking the calibration seal
- Fits into an optional magnetic hanger for easy set-up and viewing while freeing your hands for other tasks
- Presents a large digit display with bright, two-level backlight for easier reading in low light
- Includes an analog bar graph for fast changing or unstable signals
- Auto and manual ranging for maximum flexibility
- Relative mode to calculate and display difference between two readings
- Holds readings on display for safe viewing after removing probes using Touch Hold technology

### Electrical Safety

All inputs are protected to CAT IV 600 V, CAT III 1000 V. They can withstand impulses in excess of 8.000 V and reduce risks related to surges and spikes.

## Specifications: Fluke 87V/E2 Industrial Electrician Combo Kit

Specifications		
Voltage DC	<b>Maximum Voltage</b>	1000 V
	Accuracy	$\pm(0.05\% + 1)$
	Maximum Resolution	10 $\mu$ V
Voltage AC	<b>Maximum Voltage</b>	1000 V
	Accuracy	$\pm(0.7\% + 2)$ True RMS
	AC Bandwidth	20 kHz with low pass filter; 3 db @ 1 kHz
	Maximum Resolution	0.1 mV
Current DC	<b>Maximum Amps</b>	10 A (20 A for 30 seconds maximum)
	Amps Accuracy	$\pm(0.2\% + 2)$
	Maximum Resolution	0.01 $\mu$ A
Current AC	<b>Maximum Amps</b>	10 A (20 A for 30 seconds maximum)
	Amps Accuracy	$\pm(1.0\% + 2)$ True RMS
	Maximum Resolution	0.1 $\mu$ A

Resistance	<b>Maximum Resistance</b>	50 MΩ
	Accuracy	±(0.2% + 1)
	Maximum Resolution	0.1Ω
Capacitance	<b>Maximum Capacitance</b>	9,999 μF
	Accuracy	±(1% + 2)
	Maximum Resolution	0.01 nF
Frequency	<b>Maximum Frequency</b>	200 kHz
	Accuracy	±(0.005% + 1)
	Maximum Resolution	0.01 Hz
Duty Cycle	<b>Maximum Duty Cycle</b>	99.9%
	Accuracy	±(0.2% per khz + 0.1%)
	Maximum Resolution	0.1%
Temperature Measurement	-200.0°C - 1090°C -328.0°F - 1994.0°F excluding probe	
80 BK Temperature Probe	-40.0°C - 260°C -40.0°F - 500°F, 2.2°C or 2% whichever is greater	
Conductance	<b>Maximum Conductance</b>	60.00 nS
	Accuracy	±(1.0% + 10)
	Maximum Resolution	0.01 nS
Diode	<b>Range</b>	3 V
	Resolution	1 mV
	Accuracy	±(2% + 1)
Duty Cycle Range	<b>Accuracy</b>	Within ±(02% per kHz + 0.1%)
<b>Environmental Specifications</b>		
Operating Temperature	-20°C to +55°C	
Storage Temperature	-40°C to +60°C	
Humidity (Without Condensation)	0% - 90% (0°C - 35°C) 0% - 70% (35°C - 55°C)	
Operating Altitude	2000 m	
<b>Safety Specifications</b>		
Overvoltage category	EN 61010-1 to 1000 V CAT III, 600V CAT IV	
Agency Approvals	UL, CSA, TÜV, VDE listed	
<b>Mechanical and General Specifications</b>		
Size	201 x 98 x 52 mm (with holster)	
Weight	355 g 624 g - with holster	



Display	<b>Digital</b>	6000 counts updates 4/sec. 19,999 counts in high-resolution mode
	Analog	32 segments, updates 40/sec.
	Frequency	19,999 counts, updates 3/sec at > 10 Hz
Warranty	Lifetime	
Battery Life	<b>Alkaline</b>	~400 hours typical, without backlight
Shock	1 Meter drop per IEC 61010-1:2001	
Vibration	Per MIL-PRF-28800 for a Class 2 instrument	

## Ordering information



### Fluke 87V/E2 Kit

Fluke 87V/E2 Industrial Electrician Combo Kit

Includes:

- 87V Industrial Multimeter
- TL224 SureGrip™ Insulated Test Leads
- AC220 SureGrip™ Alligator Clips
- TL238 SureGrip™ Test Probes
- ToolPak™ Magnetic Meter Hanging Kit
- 80BK-A DMM Temperature Probe
- C35 Soft Carrying Case
- 9V battery (installed)

**Fluke.** *Keeping your world up and running.®*

**Fluke Europe B.V.**

P.O. Box 1186  
5602 BD Eindhoven  
The Netherlands  
[www.fluke.com/en](http://www.fluke.com/en)

©2022 Fluke Corporation. All rights reserved.  
Data subject to alteration without notice.  
01/2022

**For more information call:**

In Middle East/Africa  
+31 (0)40 267 5100

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**