

Datos técnicos

C700 Estuche rígido (serie 700)



Características principales

- **Application:** Cutouts to hold one documenting process calibrator, one Fluke Pressure Module, one BC7210 Battery Charger, one spare BP7217 Battery Pack, and test leads
- **Material:**
 - Exterior: Blow-molded charcoal gray polyethylene with textured surface
 - Interior: Black, die-cut polyurethane foam
- **Handle:** Molded polyethylene
- **Latches:** Zinc-plated steel
- **Dimensions:** 47 x 40 x 14 cm
- **Weight:** 900 g
- **One year warranty**

Descripción general del producto: C700 Estuche rígido (serie 700)

Hard carrying case with custom-cut foam liner

Modelos



Fluke C700

Fluke C700 Hard Carrying Case

Fluke. *Manteniendo su mundo en marcha.*

Fluke Ibérica, S.L.
Avda de la Industria, 32
Edificio Payma
28108 Alcobendas (Madrid)
Spain
Tel: +34 91 414 0100
E-mail: cs.es@fluke.com
www.fluke.es

©2021 Fluke Corporation. Reservados todos los derechos.
Información sujeta a modificación sin previo aviso.
12/2021

No se permite ninguna modificación de este documento sin permiso escrito de Fluke Corporation.