

Datos técnicos

SCC198 Juego de accesorios para aplicaciones automoción (serie 120)



Características principales

The SCC198 Automotive troubleshooting kit includes:

- C190 Hard-shell Carrying Case for 190-Series ScopeMeter
- SW90W FlukeView ScopeMeter Software package
- OC4USB Serial Interface Cable for connecting the ScopeMeter to a (notebook) PC
- STL90 Shielded Test Leads (1 red & 1 gray) with 2 ground leads
- Four Backprobe pins (1 red, 1 gray, 2 black),
- Four 4 mm Tip adapters (1 red, 1 gray, 2 black),
- AC85A Sets of Alligator Clips (Four pieces, 1 red, 1 gray, 2 black)
- C75 Softcase, for holding and storing all smaller items
- Low pass filter adapters (2 pieces)
- BNC(m) to BNC(f) extension cables (2 pieces)

... plus ample storage space to hold all standard accessories and manuals, included with the ScopeMeter testtool (ScopeMeter testtool not included in SCC198)

Descripción general del producto: SCC198 Juego de accesorios para

aplicaciones automoción (serie 120)

Using the ScopeMeter 190 Series in dedicated applications like automotive electronics troubleshooting, often requires special accessories like adapters, connectors and test leads to establish the measurement connection to the circuitry under test. The Fluke SCC198 kit provides a host of accessories that allow you to easily and quickly make measurements on automotive electronic systems, using a 190 Series ScopeMeter.

Modelos



Fluke SCC198

Fluke SCC198 Automotive Troubleshooting kit for 190 Series ScopeMeter
Automotive Troubleshooting kit for 190 Series ScopeMeter

The SCC198 Automotive troubleshooting kit includes:

- C190 Hard-shell Carrying Case for 190-Series ScopeMeter
- SW90W FlukeView ScopeMeter Software package
- OC4USB Serial Interface Cable for connecting the ScopeMeter to a (notebook) PC
- STL90 Shielded Test Leads (1 red and 1 gray) with 2 ground leads
- Four backprobe pins (1 red, 1 gray, 2 black)
- Four 4 mm tip adapters (1 red, 1 gray, 2 black)
- AC85A Sets of alligator clips (Four pieces, 1 red, 1 gray, 2 black)
- C75 Softcase, for holding and storing all smaller items
- Low pass filter adapters (2 pieces)
- BNC(m) to BNC(f) extension cables (2 pieces)

Plus ample storage space to hold all standard accessories and manuals, included with the ScopeMeter test tool (ScopeMeter test tool not included in SCC198)

Fluke. *Manteniendo su mundo en marcha.*

Fluke Corporation
Everett, WA 98206 EE.UU.

Para obtener información adicional En EE. UU. (800) 443-5853

En Europa/Medio Oriente/África
+31 (0)40 267 5100

En Canadá (800)-36-FLUKE
www.fluke.com

Latin America
Tel: +1 (425) 446-5500
www.fluke.com/es-gt

©2022 Fluke Corporation. Reservados todos los derechos. Impreso en los Países Bajos. Información sujeta a modificación sin previo aviso.
01/2022

No está permitido modificar este documento sin autorización por escrito de Fluke Corporation.