

Datos técnicos

Fluke Set of 3 1A/10A Current Clamps



Descripción general del producto: Fluke Set of 3 1A/10A Current Clamps

Three precision dual range current clamps (1 A/10 A) for secondary current transformer applications. For use with the 1735 and 1740 Series Power Quality Loggers. Using latest technologies (integrated memory for calibration data) provides current ranges from 0.05A up to 10A in a frequency range of 40Hz to 10kHz.

Fluke. *Manteniendo su mundo en marcha.*

Fluke Corporation

Everett, WA 98206 EE.UU.

Para obtener información adicional En EE. UU. (800) 443-5853

En Europa/Medio Oriente/África

+31 (0)40 267 5100

En Canadá (800)-36-FLUKE

www.fluke.com

Latin America

Tel: +1 (425) 446-5500

www.fluke.com/es-us

©2021 Fluke Corporation. Reservados todos los derechos. Impreso en los Países Bajos. Información sujeta a modificación sin previo aviso.
11/2021

No está permitido modificar este documento sin autorización por escrito de Fluke Corporation.