

Datos técnicos

Fluke TP84 Oxygen Sensor Insulation Piercing Clip



Características principales

- Banana jack accepts all DMM and banana jack leads
- Non-rotating banana jack prevents leads from tangling, allowing you to tighten/loosen clamp while still connected to the test lead
- Tested to 60 V DC

Descripción general del producto: Fluke TP84 Oxygen Sensor Insulation Piercing Clip

Long (30 cm, 12") piercing probe extends your reach into a hot engine. This long probe keeps your hands away from the exhaust manifold. The insulated body of the probe protects it from burning on a hot manifold.

Modelos



Fluke TP84 Oxygen Sensor Insulation Piercing Clip

Fluke. *Manteniendo su mundo en marcha.*

Fluke Corporation
Everett, WA 98206 EE.UU.

Para obtener información adicional En EE. UU. (800) 443-5853

En Europa/Medio Oriente/África
+31 (0)40 267 5100

En Canadá (800)-36-FLUKE
www.fluke.com

Latin America
Tel: +1 (425) 446-5500
www.fluke.com/es-us

©2021 Fluke Corporation. Reservados todos los derechos. Impreso en los Países Bajos. Información sujeta a modificación sin previo aviso.
12/2021

No está permitido modificar este documento sin autorización por escrito de Fluke Corporation.