

Datos técnicos

Módulo de calibración Fluke 787CAL

Características principales

Application: The calibration module provides a 9 volt dc supply to the 787. At the same time, it facilitates RS232 communication from the PC running MET/CAL to the 787 over the battery leads of the 787.

Descripción general del producto: Módulo de calibración Fluke 787CAL

Description: The Fluke 787CAL module permits users and service facilities to perform automated MET/CAL verifications and calibrations of the Fluke 787 ProcessMeter.

Note: An installation of MET/CAL Calibration Software plus appropriate calibration hardware must be provided by the user.

Modelos

Fluke 787CAL

Fluke 787CAL Calibration Module
Calibration Module

Included:

- A calibration manual
 - MET/CAL procedures
 - An interface module that permits serial communication between a 787 and a PC.
-

Fluke. *Manteniendo su mundo en marcha.*

Fluke Corporation
Everett, WA 98206 EE.UU.

Para obtener información adicional En EE. UU. (800) 443-5853

En Europa/Medio Oriente/África
+31 (0)40 267 5100

En Canadá (800)-36-FLUKE
www.fluke.com

Latin America
Tel: +1 (425) 446-5500
www.fluke.com/es-ve

©2021 Fluke Corporation. Reservados todos los derechos. Impreso en los Países Bajos. Información sujeta a modificación sin previo aviso.
11/2021

No está permitido modificar este documento sin autorización por escrito de Fluke Corporation.