

Fiche technique

C700 Mallette (série 700)



Principales fonctions

- **Application:** Cutouts to hold one documenting process calibrator, one Fluke Pressure Module, one BC7210 Battery Charger, one spare BP7217 Battery Pack, and test leads
- **Material:**
 - Exterior: Blow-molded charcoal gray polyethylene with textured surface
 - Interior: Black, die-cut polyurethane foam
- **Handle:** Molded polyethylene
- **Latches:** Zinc-plated steel
- **Dimensions:** 47 x 40 x 14 cm
- **Weight:** 900 g
- **One year warranty**

Présentation du produit: C700 Mallette (série 700)

Hard carrying case with custom-cut foam liner

Modèles



Fluke C700

Fluke C700 Hard Carrying Case

*Soyez à la pointe du progrès avec **Fluke**.*

Fluke (Switzerland) GmbH
Industrial Division
Hardstrasse 20
CH-8303 Bassersdorf
Tel: +41 (0) 44 580 7504
E-mail: roc.switzerland@fluke.com
www.fluke.com/fr-ch

©2022 Fluke Corporation. Tous droits réservés.
Informations modifiables sans préavis.
01/2022

**La modification de ce document est interdite sans
l'autorisation écrite de Fluke Corporation.**