

Kit d'accessoires automobiles pour Série 190



Principales fonctions

The SCC198 Automotive troubleshooting kit includes:

- C190 Hard-shell Carrying Case for 190-Series ScopeMeter
- SW90W FlukeView ScopeMeter Software package
- OC4USB Serial Interface Cable for connecting the ScopeMeter to a (notebook) PC
- STL90 Shielded Test Leads (1 red & 1 gray) with 2 ground leads
- Four Backprobe pins (1 red, 1 gray, 2 black),
- Four 4 mm Tip adapters (1 red, 1 gray, 2 black),
- AC85A Sets of Alligator Clips (Four pieces, 1 red, 1 gray, 2 black)
- C75 Softcase, for holding and storing all smaller items
- Low pass filter adapters (2 pieces)
- BNC(m) to BNC(f) extension cables (2 pieces)

... plus ample storage space to hold all standard accessories and manuals, included with the ScopeMeter testtool (ScopeMeter testtool not included in SCC198)

Présentation du produit: Kit d'accessoires automobiles pour Série 190

Using the ScopeMeter 190 Series in dedicated applications like automotive electronics troubleshooting, often requires special accessories like adapters, connectors and test leads to establish the measurement connection to the circuitry under

test. The Fluke SCC198 kit provides a host of accessories that allow you to easily and quickly make measurements on automotive electronic systems, using a 190 Series ScopeMeter.

Modèles



Fluke SCC198

Fluke SCC198 Automotive Troubleshooting kit for 190 Series ScopeMeter
Automotive Troubleshooting kit for 190 Series ScopeMeter

The SCC198 Automotive troubleshooting kit includes:

- C190 Hard-shell Carrying Case for 190-Series ScopeMeter
- SW90W FlukeView ScopeMeter Software package
- OC4USB Serial Interface Cable for connecting the ScopeMeter to a (notebook) PC
- STL90 Shielded Test Leads (1 red and 1 gray) with 2 ground leads
- Four backprobe pins (1 red, 1 gray, 2 black)
- Four 4 mm tip adapters (1 red, 1 gray, 2 black)
- AC85A Sets of alligator clips (Four pieces, 1 red, 1 gray, 2 black)
- C75 Softcase, for holding and storing all smaller items
- Low pass filter adapters (2 pieces)
- BNC(m) to BNC(f) extension cables (2 pieces)

Plus ample storage space to hold all standard accessories and manuals, included with the ScopeMeter test tool (ScopeMeter test tool not included in SCC198)

*Soyez à la pointe du progrès avec **Fluke**.*

Fluke (Switzerland) GmbH
Industrial Division
Hardstrasse 20
CH-8303 Bassersdorf
Tel: +41 (0) 44 580 7504
E-mail: roc.switzerland@fluke.com
www.fluke.com/fr-ch

©2022 Fluke Corporation. Tous droits réservés.
Informations modifiables sans préavis.
01/2022

**La modification de ce document est interdite sans
l'autorisation écrite de Fluke Corporation.**