

Data teknis

# Fluke BP7235 NiMH Battery Pack



## Fitur utama

7.2V 3500 mA-hour rechargeable Ni-MH battery pack. This item replaces BP7217 Ni-Cd Battery Pack

Includes one battery pack.

## Ikhtisar Produk: Fluke BP7235 NiMH Battery Pack

Description: 7.2V 3500 mA-hour rechargeable Ni-MH battery pack.

Application: Provides typical 16-hour battery life when used in 700 or 740 Calibrator.

Included: One battery pack.

Material: Six 1.2V dc Ni-MH cells in custom-molded ABS/PC-blend case.

Application: 7.1" x 2.2" x .9" (150 mm x 56 mm x 22 mm)

Dimensions: 7.1" x 2.2" x .9" (150 mm x 56 mm x 22 mm)

Weight: 11 oz/310g

Warranty: One year

## Spesifikasi: Fluke BP7235 NiMH Battery Pack

General Specifications	
Material	Six 1.2 V DC Ni-MH cells in custom-molded ABS/PC-blend case
Application	7.1 x 2.2 x .9 in (150 x 56 x 22 mm)
Dimensions	7.1 x 2.2 x .9 in (150 x 56 x 22 mm)
Weight	11 oz / 310g
Warranty	One year
This item replaces BP7217 Ni-Cd Battery Pack.	

## Model



### **Fluke BP7235**

NiMH Battery Pack

---

**Fluke.** *Memastikan aktivitas Anda terus berjalan dan beroperasi.*

**Fluke Corporation**

PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

[www.fluke.com](http://www.fluke.com)

**BUT. FLUKE SOUTH EAST ASIA PTE LTD**

Menera Satu Sentra Kelapa Gading #06-05

Jl. Bulevar Kelapa Gading Kav. LA# No. 1

Summarecon Kelapa Gading

Jakarta Utara 14240

Indonesia

Tel: +62 21 2938 5922

Email: [info.asean@fluke.com](mailto:info.asean@fluke.com)

[www.fluke.com/id](http://www.fluke.com/id)

©2021 Fluke Corporation. Specifications subject to change without notice.

11/2021

**Modification of this document is not permitted without written permission from Fluke Corporation.**