

Data teknis

# Fluke 80i-110s AC/DC Current Clamp



## Fitur utama

- Current Range: 0.1 to 100A DC or 0.1 to 70A AC
- Basic Accuracy (DC to 1kHz):
  - 100mV/A setting: 50mA to 10A +/- 3% of reading + 50mA
  - 10mV/A setting: 50mA to 40A +/- 4% of reading + 50mA
  - 40A to 80A +/- 12% of reading + 50mA
  - 80 to 100A +/- 15% of reading
- Output Signal: 10A range: 100mV/A | 100A range: 10mV/A
- Bandwidth: 1Hz to 20kHz
- Working Voltage: 600V AC rms
- Maximum Conductor Size: 11.8 mm (.46 inch) diameter
- Safety Rating: IEC 1010 and CSA-C22.2 No. 1010-1 Installation Category II, Working Voltage 600V

## Ikhtisar Produk: Fluke 80i-110s AC/DC Current Clamp

The 80i-110s is compatible with any Fluke ScopeMeter Test Tool, Power Harmonics Analyzer, Oscilloscope, Multimeter, or other voltage measurement device that has the following features: BNC input connectors or if using a meter convert the banana plugs to a BNC connector using the adapter PM9081/001.

[Useful resources and rugged tools for Solar professionals](#)

## Spesifikasi: Fluke 80i-110s AC/DC Current Clamp

Specifications	
Nominal current range	10 A, AC/DC
	100 A, AC/DC
Continuous current range	0.1 A - 10 A AC/DC
	1 A - 100 A AC/DC
Maximum non-destructive current	140 A - 2 kHz
Lowest measurable current	0.1 A
Basic accuracy	100 mV/A setting: 50 mA to 10 A $\pm 3\%$ of reading +50 mA
	10 mV/A setting: 50 mA to 40 A $\pm 4\%$ of reading +50 mA
	40 A to 80 A $\pm 12\%$ of reading +50 mA
	80 to 100 A $\pm 15\%$ of reading
Useable frequency	DC - 100 kHz
Output level(s)	10 A range: 100 mV/A
	100 A range: 10 mV/A
Zero error adjustment	Yes
Safety Specifications	
Safety	CAT II, 600 V
	CAT III, 300 V
Maximum voltage	600 V
Mechanical and General Specifications	
Warranty	1 year
Battery life	9 V, 55 h
Maximum conductor diameter	11.8 mm
Output cable length	1.6 m
BNC adapter	Yes

## Model



**Fluke 80i 110s**

---

**Fluke.** *Memastikan aktivitas Anda terus berjalan dan beroperasi.*

**Fluke Corporation**

PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

[www.fluke.com](http://www.fluke.com)

**BUT. FLUKE SOUTH EAST ASIA PTE LTD**

Menera Satu Sentra Kelapa Gading #06-05

Jl. Bulevar Kelapa Gading Kav. LA# No. 1

Summarecon Kelapa Gading

Jakarta Utara 14240

Indonesia

Tel: +62 21 2938 5922

Email: [info.asean@fluke.com](mailto:info.asean@fluke.com)

[www.fluke.com/id](http://www.fluke.com/id)

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

**Modification of this document is not permitted without written permission from Fluke Corporation.**