

Data teknis

Fluke i1010-KIT AC/DC Current Clamp and Carry Case Kit



Ikhtisar Produk: Fluke i1010-KIT AC/DC Current Clamp and Carry Case Kit

Special value kit for electrical professional who is looking to add on DC and AC current measurement capabilities to their DMM. Includes a roomy carry case to hold and protect your meter and current clamp, plus extra storage for your test leads, probes and manuals.

Model



Fluke i1010 Kit

- i1010 1-600A AC rms, 1-1000A DC Current Clamp
- Zippered vinyl carry case with moveable divider

Fluke. Memastikan aktivitas Anda terus berjalan dan beroperasi.

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

www.fluke.com

BUT. FLUKE SOUTH EAST ASIA PTE LTD

Menera Satu Sentra Kelapa Gading #06-05

Jl. Bulevar Kelapa Gading Kav. LA# No. 1

Summarecon Kelapa Gading

Jakarta Utara 14240

Indonesia

Tel: +62 21 2938 5922

Email: info.asean@fluke.com

www.fluke.com/id

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.