

Data teknis

Fluke i17XX-flex1500/4pk iFlex® Current Clamps



Ikhtisar Produk: Fluke i17XX-flex1500/4pk iFlex® Current Clamps

Probe arus fleksibel iFlex 12 inci untuk Fluke 17XX ini memperluas rentang pengukuran Energy atau Power Logger Fluke 17XX hingga 1500 A ac sekaligus menyediakan fleksibilitas pengukuran terunggul. Probe iFlex ini terhubung langsung ke logger, yang menampilkan pengukuran arus tanpa faktor penskalaan yang rentan kesalahan. Kabel sepanjang 1,8 m (6 kaki) memungkinkan pemisahan antara lokasi pengukuran dan pencatat energi sehingga lebih mudah untuk melihat tampilan. Kabel iFlex Fluke 17XX tersedia dalam model 12, 24, dan 36 inci

Model



i17XX-flex1500/4pk

1500A 12 inch, 4 pack iFlex® Current Clamps

Fluke. Memastikan aktivitas Anda terus berjalan dan beroperasi.

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

BUT. FLUKE SOUTH EAST ASIA PTE LTD
Menera Satu Sentra Kelapa Gading #06-05
JI. Bulevar Kelapa Gading Kav. LA# No. 1
Summarecon Kelapa Gading
Jakarta Utara 14240
Indonesia
Tel: +62 21 2938 5922
Email: info.asean@fluke.com
www.fluke.com/id
©2021 Fluke Corporation. Specifications subject to
change without notice.
11/2021

**Modification of this document is not permitted
without written permission from Fluke Corporation.**