

Data teknis

## Penjepit Arus iFlex® Fluke i17XX-flex3000/4pk



### Ikhtisar Produk: Penjepit Arus iFlex® Fluke i17XX-flex3000/4pk

Probe arus fleksibel iFlex 24 inci untuk Fluke 17XX ini memperluas rentang pengukuran Energy atau Power Logger Fluke 17XX hingga 3000 A ac sekaligus menyediakan fleksibilitas pengukuran terunggul. Probe iFlex ini terhubung langsung ke pencatat energi, menampilkan pengukuran arus tanpa faktor penskalaan yang rentan kesalahan. Kabel sepanjang 1,8 m (6 kaki) memungkinkan pemisahan antara lokasi pengukuran dan pencatat energi sehingga lebih mudah untuk melihat tampilan. Kabel iFlex Fluke 17XX tersedia dalam model 12, 24, dan 36 inci.

## Model



### **i17XX-flex3000/4pk**

3000A 24 inch, 4 pack iFlex® Current Clamps

---

**Fluke. Memastikan aktivitas Anda terus berjalan dan beroperasi.**

**Fluke Corporation**

PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

[www.fluke.com](http://www.fluke.com)

**BUT. FLUKE SOUTH EAST ASIA PTE LTD**

Menera Satu Sentra Kelapa Gading #06-05

Jl. Bulevar Kelapa Gading Kav. LA# No. 1

Summarecon Kelapa Gading

Jakarta Utara 14240

Indonesia

Tel: +62 21 2938 5922

Email: [info.asean@fluke.com](mailto:info.asean@fluke.com)

[www.fluke.com/id](http://www.fluke.com/id)

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

**Modification of this document is not permitted without written permission from Fluke Corporation.**