

Data teknis

Fluke MBX 300 Poleset Mounting Kit



Ikhtisar Produk: Fluke MBX 300 Poleset Mounting Kit

Built with all-weather IP65 enclosures, the Fluke 1743 and 1744 Power Quality Loggers are ready to be installed wherever the job demands. With the durable mounting kit, the Fluke 1743 and 1744 can be easily and safely secured to utility poles or suspended from other hardware. The package includes a mounting plate and strap that affix with existing fasteners and attachment points on the loggers.

Model



Fluke 1743/44 Poleset

Fluke MBX 300 Poleset Mounting Kit

Fluke MBX Clamp 1A/10A

Fluke Set of 3 1A/10A Current Clamps

Fluke. *Memastikan aktivitas Anda terus berjalan dan beroperasi.*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

www.fluke.com

BUT. FLUKE SOUTH EAST ASIA PTE LTD

Menera Satu Sentra Kelapa Gading #06-05

Jl. Bulevar Kelapa Gading Kav. LA# No. 1

Summarecon Kelapa Gading

Jakarta Utara 14240

Indonesia

Tel: +62 21 2938 5922

Email: info.asean@fluke.com

www.fluke.com/id

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.