

Data teknis

Fluke TLK282 SureGrip™ Deluxe Automotive Test Lead Kit



Fitur utama

Everything you can find in the TLK281 Automotive Test Lead Kit, plus a few extras. Use the back probe pins to slide into weather pack connectors on fuel injectors, TPS and MAP sensors. A hook probe with plunger actuation allows quick connection to pins or exposed conductors.

- Tested to 60 V DC

Ikhtisar Produk: Fluke TLK282 SureGrip™ Deluxe Automotive Test Lead Kit

Everything you can find in the TLK281 Automotive Test Lead Kit, plus a few extras. Use the back probe pins to slide into weather pack connectors on fuel injectors, TPS and MAP sensors. A hook probe with plunger actuation allows quick connection to pins or exposed conductors.

Model



Fluke TLK282

SureGrip™ Deluxe Automotive Test Lead Kit

Kit contains:

- TP81 Insulation Piercing Clip Set
- TP40 Automotive Back Probe Pins (five)
- TL224 Suregrip™ Silicone Test Lead Set
- TP220 Suregrip™ Test Probe Set
- AC220 Suregrip™ Alligator Clip Set
- AC285 Suregrip™ Large Jaw Alligator Clip Set
- AC280 Suregrip™ Hook Clip Set
- Soft Case

Fluke. *Memastikan aktivitas Anda terus berjalan dan beroperasi.*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

www.fluke.com

BUT. FLUKE SOUTH EAST ASIA PTE LTD

Menera Satu Sentra Kelapa Gading #06-05

Jl. Bulevar Kelapa Gading Kav. LA# No. 1

Summarecon Kelapa Gading

Jakarta Utara 14240

Indonesia

Tel: +62 21 2938 5922

Email: info.asean@fluke.com

www.fluke.com/id

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.