

Data teknis

## Lensa Inframerah Macro 3



### Ikhtisar Produk: Lensa Inframerah Macro 3

Lensa makro close up (0,5x) untuk pemeriksaan dan analisis subjek lebih kecil dalam aplikasi penelitian dan pengembangan – kompatibel dengan model TiX1000, TiX660, dan TiX640.

Aplikasi: Penelitian dan pengembangan, target sangat kecil, papan PCB (disipasi panas), substrat semikonduktor, dan segel.

### Spesifikasi: Lensa Inframerah Macro 3

<b>Karakteristik Umum</b>	
Deskripsi lensa	Close-up 0,5x
Jarak fokus	60 mm
Fokus	100 mm
<b>1024 x 768</b>	
iFOV (°)	35,1 x 26,5 mRad
Resolusi	35 µm
<b>640 x 480</b>	
iFOV (°)	32,3 x 24,4 mRad
Resolusi	50 µm

## Model



### **FLK-Xlens/Macro3**

Close-up 0.5 times

---

Applications: Research and development, extremely small targets, PCB boards (heat dissipation), semiconductor substrates, and seals.

Compatible with TiX1000, TiX660 and TiX640 infrared cameras.

Macro 3 lens must be used with the Telephoto lens (FLK-Xlens-Tele).

---

**Fluke.** *Memastikan aktivitas Anda terus berjalan dan beroperasi.*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Europe/M-East/Africa  
+31 (0)40 267 5100  
In Canada (800)-36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

**BUT. FLUKE SOUTH EAST ASIA PTE LTD**  
Menera Satu Sentra Kelapa Gading #06-05  
JI. Bulevar Kelapa Gading Kav. LA# No. 1  
Summarecon Kelapa Gading  
Jakarta Utara 14240  
Indonesia  
Tel: +62 21 2938 5922  
Email: [info.asean@fluke.com](mailto:info.asean@fluke.com)  
[www.fluke.com/id](http://www.fluke.com/id)  
©2021 Fluke Corporation. Specifications subject to  
change without notice.  
11/2021

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**