

Data teknis

Lensa Inframerah Sudut Lebar



Ikhtisar Produk: Lensa Inframerah Sudut Lebar

Bidang pandang yang lebar untuk pemeriksaan objek besar – kompatibel dengan model TiX1000, TiX660, dan TiX640.

Aplikasi: Seluruh dinding atau sisi gedung atau kebutuhan bekerja di tempat yang sempit.

Spesifikasi: Lensa Inframerah Sudut Lebar

Karakteristik Umum	
Deskripsi lensa	Lensa sudut lebar
Jarak fokus	15 mm
Fokus	0,47 m
1024 x 768	
iFOV	1,1 mRad
FOV	68,7 x 50,7°
640 x 480	
iFOV	1,7 mRad
FOV	62,3 x 46,4°

Model



FLK-Xlens/Wide

Applications: Entire wall or side of building or the need to work in tight spaces.
Compatible with TiX1000, TiX660 and TiX640 infrared cameras.

Fluke. *Memastikan aktivitas Anda terus berjalan dan beroperasi.*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

www.fluke.com

BUT. FLUKE SOUTH EAST ASIA PTE LTD

Menera Satu Sentra Kelapa Gading #06-05

Jl. Bulevar Kelapa Gading Kav. LA# No. 1

Summarecon Kelapa Gading

Jakarta Utara 14240

Indonesia

Tel: +62 21 2938 5922

Email: info.asean@fluke.com

www.fluke.com/id

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

Modification of this document is not permitted without written permission from Fluke Corporation.