

Data teknis

## P5543 Angle Adapter



### Ikhtisar Produk: P5543 Angle Adapter

To calibrate gauges with the pressure connection on the rear (e.g. panel mount gauges) In their correct operating position, an angle adaptor should be used. The angle adaptor uses the standard gauge adapters and positions the gauges at 90°. The maximum working pressure of this unit is 10,000 psi (700 bar).

### Spesifikasi: P5543 Angle Adapter

<b>Specifications</b>	
<b>Body materials</b>	Stainless steel
<b>O-Rings</b>	Nitrile
<b>Test Port Adapters</b>	As supplied with calibrator
<b>Calibrator Connection</b>	3/8 BSP male (mating adapter supplied)

## Model

**P5543**

P5543 Angle Adapter

---

Angle Adapter

---

**Fluke.** *Memastikan aktivitas Anda terus berjalan dan beroperasi.*

**Fluke Corporation**

PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

[www.fluke.com](http://www.fluke.com)

**BUT. FLUKE SOUTH EAST ASIA PTE LTD**

Menera Satu Sentra Kelapa Gading #06-05

Jl. Bulevar Kelapa Gading Kav. LA# No. 1

Summarecon Kelapa Gading

Jakarta Utara 14240

Indonesia

Tel: +62 21 2938 5922

Email: [info.asean@fluke.com](mailto:info.asean@fluke.com)

[www.fluke.com/id](http://www.fluke.com/id)

©2021 Fluke Corporation. Specifications subject to change without notice.

12/2021

**Modification of this document is not permitted without written permission from Fluke Corporation.**