

Data teknis

Fluke 1587 MDT: Advanced Motor and Drive Troubleshooting Kit



Fitur utama

Includes a Fluke 1587 Insulation Multimeter, Fluke i400 Current Clamp, and a Fluke 9040 Phase Rotation Indicator.

- With the Fluke 1587, perform insulation tests, plus a wide-range of DMM tasks with confidence and ease.
- Use the Fluke i400 with your Fluke 1587 to accurately measure AC current without breaking the circuit.
- Check the rotation of three-phase motors easily and safely with the Fluke 9040.

Ikhtisar Produk: Fluke 1587 MDT: Advanced Motor and Drive Troubleshooting Kit

Produk dalam kit ini telah dipilih secara khusus untuk aplikasi pemecahan masalah dan maintenance.

Membuat program maintenance menjadi penting untuk memelihara waktu kerja peralatan listrik dan secara signifikan dapat mengurangi waktu henti yang direncanakan dan tidak direncanakan. Biaya waktu henti yang tidak direncanakan sulit untuk dihitung, namun sering kali signifikan. Untuk beberapa industri, hal ini dapat menunjukkan 1% - 3% pendapatan (dengan potensi 30% - 40% laba) setiap tahun.

Termasuk Multimeter Insulation Fluke 1587, Klem Arus Fluke i400, dan Indikator Rotasi fasa Fluke 9040.

- Dengan Fluke 1587, lakukan uji Insulation dan berbagai tugas DMM dengan yakin dan mudah.

- Gunakan Fluke i400 bersama dengan Fluke 1587 untuk mengukur arus AC secara akurat tanpa merusak sirkuit
- Periksa rotasi motor tiga fasa dengan mudah dan aman menggunakan Fluke 9040

Multimeter Insulation Fluke 1587

- Dua produk dalam satu perangkat: [Insulation Tester](#) dan Multimeter Berfitur lengkap yang canggih
- Cocok untuk mengerjakan motor, kabel, dan switch gear
- Tampilan besar dengan backlight
- Filter untuk pengukuran penggerak motor
- Uji Insulation (0,01 MΩ s/d 2 GΩ)
- Tegangan uji Insulation (50 V, 100 V, 250 V, 500 V, 1.000 V) untuk berbagai aplikasi
- Peringkat tegangan berlebih CAT III 1.000 V /CAT IV 600 V untuk perlindungan pengguna tambahan
- Garansi 3 tahun

[Complete specifications](#)

Klem Arus Fluke i400

- Gunakan dengan Fluke 1587 untuk mengukur 1A AC hingga 400 A AC
- Output 1 mA/Amp menjamin pembacaan yang mudah
- Peringkat tegangan berlebih CAT III 1.000 V / CAT IV 600 V untuk perlindungan pengguna tambahan
- Dirancang khusus untuk menawarkan utilitas maksimum dengan bentuk yang sangat ringkas
- Konduktor maksimum: Ø 32 mm
- Garansi 1 tahun

[Complete specifications](#)

Indikator Rotasi Fasa Fluke 9040

- Tampilan besar agar dapat menentukan rotasi medan dan urutan fasa dengan mudah
- Indikator untuk ketiga fasa
- Peringkat tegangan berlebih CAT III 600 V
- Garansi 2 tahun

[Complete specifications](#)

Spesifikasi: Fluke 1587 MDT: Advanced Motor and Drive Troubleshooting Kit

Includes a Fluke 1587 Insulation Multimeter, Fluke i400 Current Clamp, and a Fluke 9040 Phase Rotation Indicator.

Fluke 1587 Insulation Multimeter

- Two products in one: Powerful [Insulation Tester](#) and Full-featured Multimeter
- Ideal for work on motors, cables, and switch gear
- Large display with backlight
- Filter for motor drive measurements
- Insulation test (0.01 MΩ to 2 GΩ)
- Insulation test voltages (50 V, 100 V, 250 V, 500 V, 1000 V) for many applications
- CAT III 1000 V /CAT IV 600 V overvoltage rating for added user protection
- 3 year warranty

Complete specifications

[Fluke i400 AC Current Clamp](#)

- Use with your Fluke 1587 to measure 1A AC to 400 A AC
- 1 mA/Amp output guarantees easy reading
- CAT III 1000 V / CAT IV 600 V overvoltage rating for added user protection
- Specially designed to offer maximum utility in a very compact shape
- Maximum conductor: Ø 32 mm
- 1 year warranty

[Complete specifications](#)

[Fluke 9040 Phase Rotation Indicator](#)

- Large display to easily determine field rotation and phase sequence
- Indication for all three phases
- CAT III 600 V overvoltage rating
- 2 year warranty

[Complete specifications](#)

Model



Fluke 1587/MDT Kit

Fluke 1587/MDT Advanced Motor and Drive Troubleshooting Kit

Includes:

- Fluke 1587 Insulation Multimeter
 - Fluke i400 Current Clamp
 - Fluke 9040 Phase Rotation Indicator
-

Fluke. *Memastikan aktivitas Anda terus berjalan dan beroperasi.*

Fluke Corporation

PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:

In the U.S.A. (800) 443-5853

In Europe/M-East/Africa

+31 (0)40 267 5100

In Canada (800)-36-FLUKE

From other countries +1 (425) 446-5500

www.fluke.com

BUT. FLUKE SOUTH EAST ASIA PTE LTD

Menera Satu Sentra Kelapa Gading #06-05

Jl. Bulevar Kelapa Gading Kav. LA# No. 1

Summarecon Kelapa Gading

Jakarta Utara 14240

Indonesia

Tel: +62 21 2938 5922

Email: info.asean@fluke.com

www.fluke.com/id

©2022 Fluke Corporation. Specifications subject to change without notice.

01/2022

Modification of this document is not permitted without written permission from Fluke Corporation.