

Dati tecnici

Set di sonde per tensione ScopeMeter VPS420-G

Modelli

Fluke VPS420-G

Ruggedized High-Working ScopeMeter Voltage Probe Set

Grey/black, 100:1, 150 MHz, 1000V CAT III / 600V CAT IV, working voltage (voltage between probe tip and reference lead): 2000V CAT III / 1200V CAT IV.

Fluke. *Keeping your world up and running.®*

Fluke Italia S.r.l.
Viale Lombardia 218
20861 Brugherio (MB)
Tel: +39 02 3600 2000
E-mail: cs.it@fluke.com
www.fluke.it

©2022 Fluke Corporation. Tutti i diritti riservati.
Dati passibili di modifiche senza preavviso.
01/2022

**Non sono ammesse modifiche al presente
documento senza autorizzazione scritta da parte di
Fluke Corporation.**