

Technische gegevens

700BCW Barcodelezer



Productoverzicht: 700BCW Barcodelezer

Description: This Hewlett Packard HBSW-8200 Bar Code Wand reads eight common bar code symbologies. Code 39, Interleave 2 or 5, UPC A and E, EAN 8 and 13, Codabar, Code 128, Code 11, Code 93, and MSI Code. Programmable via bar code labels or escape sequences. LED indicates when a bar code has been correctly decoded. Resolution, 0.19 mm. Usable from -20 °C to 65 °C, in ambient light to 100,00 lux. EMI compliance per FCC part 15 Class B. ESD immunity, 25 kV.

Application: Supports the scanned entry of procedure identification, tag ID, serial number, and operator ID to a Fluke 743 Documenting Process Calibrator.

Specificaties: 700BCW Barcodelezer

Mechanical and General Specifications	
Size	160 x 23 mm. Coiled cable extends to approximately 2.5 m
Weight	160 g
Warranty	One year
Material	Polycarbonate wand, sapphire tip

Modellen



Fluke 700BCW

Bar Code Wand

Included:

- Bar code wand with integrated decoding circuitry, holder, and users manual
 - Fluke 700BCA Bar Code Adapter
 - Instruction sheet in English, French, German, Italian, and Spanish.
-

Fluke. *Keeping your world up and running.*®

Fluke Nederland B.V.
Postbus 1337
5602 BH Eindhoven
Tel: +31 40 267 5100
E-mail: cs.nl@fluke.com
www.fluke.nl

©2022 Fluke Corporation. Alle rechten
voorbehouden.
Wijzigingen zonder voorafgaande kennisgeving
voorbehouden.
01/2022

**Wijziging van dit document is niet toegestaan
zonder schriftelijke toestemming van Fluke
Corporation.**