

Tekniske data

700BCA Strekkodeadapter



Produktoversikt: 700BCA Strekkodeadapter

Description: Shielded four conductor cable terminated with a 9-socket D-subminiature connector and a 9-pin D-subminiature connector.

Application: Provides interconnection and pin translation between a Fluke 743 Documenting Process Calibrator and a Hewlett Packard HBSW-8200 Bar Code Wand.

Spesifikasjoner: 700BCA Strekkodeadapter

Mechanical and General Specifications

Size	Overall length approximately 15 cm
Warranty	One year
Material	Black PVC cable and housings, tin plated shells, gold plated copper contacts

Modeller



Fluke 700BCA

Bar Code Adapter

-
- Interface cable
 - Calibrator to bar code wand
 - Instruction sheet in English, French, German, Italian, and Spanish.
-

Fluke. *Keeping your world up and running.*®

Fluke Norge AS
Postboks 383
1411 Kolbotn
Tlf: 800 18 227
E-mail: cs.no@fluke.com
www.fluke.no

©2021 Fluke Corporation. Med enerett.
Informasjonen kan endres uten varsel. Vi tar
forbehold om trykkfeil.
12/2021

**Endring av dette dokumentet er ikke tillatt uten
skriftlig tillatelse fra Fluke Corporation.**