


Tekniske data

Fluke MA190 Accessory Kit for Medical and Video Applications



Nøkkelfunksjoner

This kit includes:

- 50 Ohm BNC insulated feedthrough terminator
- 50 Ohm BNC terminator with 10:1 signal attenuation
- 1 Ohm current shunt for current measurements
- Safety-designed BNC cable, 1.5 m (5 ft)
- Insulated BNC (f) to 4 mm-banana plug adapter
- Dual 4 mm banana receptacles (1 red, 1 black)

Produktoversikt: Fluke MA190 Accessory Kit for Medical and Video Applications

The MA190 accessory set enables interconnection of the Fluke ScopeMeter 190 Series for use in the field of Medical Imaging and Video systems.

Modeller



Fluke MA190

Accessory kit for medical and video applications

Fluke MA190 Accessory Kit for Medical and Video Applications

Fluke. *Keeping your world up and running.®*

Fluke Norge AS
Postboks 383
1411 Kolbotn
Tlf: 800 18 227
E-mail: cs.no@fluke.com
www.fluke.no

©2021 Fluke Corporation. Med enerett.
Informasjonen kan endres uten varsel. Vi tar
forbehold om trykkfeil.
12/2021

**Endring av dette dokumentet er ikke tillatt uten
skriftlig tillatelse fra Fluke Corporation.**