


Tekniske data

VPS420-R robust probe for høy driftsspenning, sett 100:1



Modeller



Fluke VPS420-R

Ruggedized High-Working ScopeMeter Voltage Probe Set

red/black, 100:1, 150 MHz, 1000V CAT III / 600V CAT IV, working voltage (voltage between probe tip and reference lead): 2000V CAT III / 1200V CAT IV.

Fluke. *Keeping your world up and running.*®

Fluke Norge AS
Postboks 383
1411 Kolbotn
Tlf: 800 18 227
E-mail: cs.no@fluke.com
www.fluke.no

©2021 Fluke Corporation. Med enerett.
Informasjonen kan endres uten varsel. Vi tar
forbehold om trykkfeil.
12/2021

**Endring av dette dokumentet er ikke tillatt uten
skriftlig tillatelse fra Fluke Corporation.**