

# Elektrisk testerpakke med hylster og 1AC II



## Nøkkelfunksjoner

- T5-1000 electrical tester automatically measures volts AC and volts DC with precise digital resolution
- Includes easy, accurate OpenJaw™ current measurement
- Displays resistance to 1000  $\Omega$
- Includes a continuity beeper for quick go/no-go tests
- All inputs are protected to EN61010-1 CAT III 1000 V CAT IV 600 V. UL, CSA
- 1AC II offers Voltbeat™ technology and continuous self-test so you always know it's working
- Upon detection of voltage, the VoltAlert™ tip glows and beeper sounds
- CAT IV 1000 V for added protection

## Produktoversikt: Elektrisk testerpakke med hylster og 1AC II

Spennings-, kontinuitets- og strømtestersett med hylster. 1AC følger med på kjøpet.

## Modeller



### Fluke T5-H5-1AC II Kit

---

This kit includes:

- Fluke T5-1000
  - Fluke 1AC II
  - H5
-

**Fluke.** *Keeping your world up and running.*®

**Fluke Norge AS**  
Postboks 383  
1411 Kolbotn  
Tlf: 800 18 227  
E-mail: [cs.no@fluke.com](mailto:cs.no@fluke.com)  
[www.fluke.no](http://www.fluke.no)

©2021 Fluke Corporation. Med enerett.  
Informasjonen kan endres uten varsel. Vi tar  
forbehold om trykkfeil.  
12/2021

**Endring av dette dokumentet er ikke tillatt uten  
skriftlig tillatelse fra Fluke Corporation.**