

Dane techniczne

Walizka C700 do serii 700



Najważniejsze cechy

- **Application:** Cutouts to hold one documenting process calibrator, one Fluke Pressure Module, one BC7210 Battery Charger, one spare BP7217 Battery Pack, and test leads
- **Material:**
 - Exterior: Blow-molded charcoal gray polyethylene with textured surface
 - Interior: Black, die-cut polyurethane foam
- **Handle:** Molded polyethylene
- **Latches:** Zinc-plated steel
- **Dimensions:** 47 x 40 x 14 cm
- **Weight:** 900 g
- **One year warranty**

Omówienie produktu: Walizka C700 do serii 700

Hard carrying case with custom-cut foam liner

Modele



Fluke C700

Fluke C700 Hard Carrying Case

Fluke. *Keeping your world up and running.®*

Fluke Europe B.V.
P.O. Box 1186
5602 BD Eindhoven
The Netherlands
Tel: +31 4 0267 5406
E-mail cee.cs@fluke.com
www.fluke.pl

©2022 Fluke Corporation. Wszelkie prawa
zastrzeżone.
Dane mogą ulec zmianie bez uprzedzenia.
01/2022

**Modyfikacja niniejszego dokumentu bez pisemnej
zgody Fluke Corporation jest zabroniona.**