

Dane techniczne

Cęgi prądowe AC/DC i410-KIT z miękkim futerałem



Omówienie produktu: Cęgi prądowe AC/DC i410-KIT z miękkim futerałem

Special value kit for electrical professional who is looking to add on DC and AC current measurement capabilities to their DMM. Includes a roomy carry case to hold and protect your meter and current clamp, plus extra storage for your test leads, probes and manuals.

Modele



Fluke i410 Kit

- [i410](#) 1-400A AC rms, 1-400A DC Current Clamp
- Zippered vinyl carry case with moveable divider

Fluke. *Keeping your world up and running.®*

Fluke Europe B.V.
P.O. Box 1186
5602 BD Eindhoven
The Netherlands
Tel: +31 4 0267 5406
E-mail cee.cs@fluke.com
www.fluke.pl

©2022 Fluke Corporation. Wszelkie prawa
zastrzeżone.
Dane mogą ulec zmianie bez uprzedzenia.
01/2022

**Modyfikacja niniejszego dokumentu bez pisemnej
zgody Fluke Corporation jest zabroniona.**