

Dados técnicos

FOM Medidor de fibra óptica



Informações gerais sobre o produto: FOM Medidor de fibra óptica

The Fluke Fiber Optic Meter (FOM) helps you test and maintain fiber optic cable without having to buy a whole new meter. Plug the FOM directly into any DMM with a mV dc function and a 10 M Ω input impedance and quickly and accurately verify fiber optic cable system loss. Light sources and patch cords sold separately.

Modelos



Fluke FOM

Fluke FOM Fiber Optic Meter

Fluke. *Keeping your world up and running.*®

Fluke Corporation

PO Box 9090, Everett, WA 98206 EUA

Para obter mais informações, ligue para os seguintes números:

Tel: (11) 3530-8901

Email: info@fluke.com.br

www.fluke.com/pt-br

Fluke do Brasil Ltda

CENESP Av. Maria Coelho Aguiar,

215 – Bloco G, 1º andar

São Paulo/SP – CEP: 05804-900

©2021 Fluke Corporation. Todos os direitos reservados. Os dados fornecidos estão sujeitos a alterações sem aviso prévio.
12/2021

É proibido modificar este documento sem permissão escrita da Fluke Corporation.