


Dados técnicos


## Fluke 3210-PR-TF 1000A Flex Thin Flex Current Probe (24 inch/60cm)



### Informações gerais sobre o produto: Fluke 3210-PR-TF 1000A Flex Thin Flex Current Probe (24 inch/60cm)

The Fluke 3210-PR-TF 1000A Flex Thin Flex Current Probe is an ac current probe utilizing the Rogowski principle. The Fluke 3210PRTF Probe is designed for use with the Fluke 1750 Power Recorder and measures current from very low frequencies up to the 50th harmonic of a 50/60 Hz power supply. The flexible and lightweight measuring head allows quick and easy installation in hard to reach areas and around large conductors.

## Modelos



### **Fluke 3210-PR-TF**

1000A Flex Thin Flex Current Probe (24 inch/60cm)

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 EUA

**Para obter mais informações, ligue para os seguintes números:**

Tel: (11) 3530-8901  
Email: [info@fluke.com.br](mailto:info@fluke.com.br)  
[www.fluke.com/pt-br](http://www.fluke.com/pt-br)

**Fluke do Brasil Ltda**  
CENESP Av. Maria Coelho Aguiar,  
215 – Bloco G, 1º andar  
São Paulo/SP – CEP: 05804-900

©2021 Fluke Corporation. Todos os direitos reservados. Os dados fornecidos estão sujeitos a alterações sem aviso prévio.  
12/2021

**É proibido modificar este documento sem permissão escrita da Fluke Corporation.**