

Dados técnicos

Kit de verificador eléctrico com bolsa e Fluke 1AC II



Principais recursos

- T5-1000 electrical tester automatically measures volts AC and volts DC with precise digital resolution
- Includes easy, accurate OpenJaw™ current measurement
- Displays resistance to 1000 Ω
- Includes a continuity beeper for quick go/no-go tests
- All inputs are protected to EN61010-1 CAT III 1000 V CAT IV 600 V. UL, CSA
- 1AC II offers Voltbeat™ technology and continuous self-test so you always know it's working
- Upon detection of voltage, the VoltAlert™ tip glows and beeper sounds
- CAT IV 1000 V for added protection

Informações gerais sobre o produto: Kit de verificador eléctrico com bolsa e Fluke 1AC II

Kit de verificador de tensão, continuidade e corrente com estojo. O 1AC é grátis.

Modelos



Fluke T5-H5-1AC II Kit

This kit includes:

- Fluke T5-1000
 - Fluke 1AC II
 - H5
-

Fluke. *Keeping your world up and running.*®

Fluke Corporation
PO Box 9090, Everett, WA 98206 EUA

Para obter mais informações, ligue para os seguintes números:
Tel: (11) 3530-8901
Email: info@fluke.com.br
www.fluke.com/pt-br

Fluke do Brasil Ltda
CENESP Av. Maria Coelho Aguiar,
215 – Bloco G, 1º andar
São Paulo/SP – CEP: 05804-900
©2021 Fluke Corporation. Todos os direitos reservados. Os dados fornecidos estão sujeitos a alterações sem aviso prévio.
10/2021

É proibido modificar este documento sem permissão escrita da Fluke Corporation.