

Dados técnicos

# Fluke BP7235 NiMH Battery Pack



## Características principais

7.2V 3500 mA-hour rechargeable Ni-MH battery pack. This item replaces BP7217 Ni-Cd Battery Pack

Includes one battery pack.

## Descrição do produto: Fluke BP7235 NiMH Battery Pack

7.2 V 3500 mA-hour rechargeable Ni-MH battery pack. Provides typical 16-hour battery life when used in 700 or 740 Calibrator.

## Especificações: Fluke BP7235 NiMH Battery Pack

| General Specifications |   |
|------------------------|---|
| Material               | Six 1.2 V DC Ni-MH cells in custom-molded ABS/PC-blend case |
| Application            | 7.1 x 2.2 x .9 in (150 x 56 x 22 mm)                        |
| Dimensions             | 7.1 x 2.2 x .9 in (150 x 56 x 22 mm)                        |
| Weight                 | 11 oz / 310g  |
| Warranty               | One year  |

This item replaces BP7217 Ni-Cd Battery Pack.

## Modelos



### Fluke BP7235

NiMH Battery Pack

---

**Fluke.** *Keeping your world up and running.®*

**Fluke Ibérica, S.L.**

Pol. Ind. Valportillo  
C/ Valgrande, 8  
Ed. Thanworth II · Nave B1A  
28108 Alcobendas  
Madrid  
Tel: +34 91 414 0100  
E-mail: [cs.es@fluke.com](mailto:cs.es@fluke.com)  
[www.fluke.pt](http://www.fluke.pt)

©2022 Fluke Corporation. Todos os direitos reservados.

Os dados fornecidos estão sujeitos a alterações sem aviso prévio.  
01/2022

**AresAgante, Lda.**

Rua Caminho das Congostas, 320  
4250-159 Porto  
Tel: +351 2 2832 9400  
E-mail: [geral@aresagante.pt](mailto:geral@aresagante.pt)  
[www.aresagante.pt](http://www.aresagante.pt)

**A modificação deste documento não é permitida sem a autorização escrita da Fluke Corporation.**