

PV350 Модуль измерения давления и вакуума



Ключевые особенности

- Compatible with all Fluke and most popular DMMs
- Digital pressure and vacuum measurements in a single module
- Transducer sealed in 316 stainless steel compatible with variety of liquids and gases
- Measures vacuum to 76 cm Hg
- Displays results in English (psig of Hg) or metric (kPa or cm Hg) units
- Measures pressure to 3447 kPa (500 psig)
- One year warranty

Модели



Fluke. Keeping your world up and running.®

ООО «Флюк СИИЭС»
125993, г. Москва, Ленинградский
проспект д. 37 к. 9 подъезд 4, 1 этаж,
БЦ «Аэростар»
Тел: +7 (495) 664-75-12
Факс: +7 (495) 664-75-12
e-mail: info@fluke.ru

© Авторское право 2021 Fluke Corporation.
Авторские права защищены. Данные могут
быть изменены без уведомления.
Самые надежные инструменты в мире
12/2021

**Не разрешается вносить изменения в данный
документ без письменного согласия компании
Fluke Corporation.**