

Технические данные


## Fluke i1730-flex6000 iFlex® Current Clamp



### Обзор прибора: Fluke i1730-flex6000 iFlex® Current Clamp

The Fluke 1730 Energy Logger 36 inch iFlex® flexible current probes expand the measurement range of the Fluke 1730 to 6000A AC while providing the ultimate measurement flexibility. The iFlex® probes connect directly to the energy logger, displaying current measurements without error prone scaling factors. The 1.8 m (6 ft) cord allows separation between the measurement location and the energy logger making it easier to view the display. Fluke 1730 Energy Logger iFlex® cables are available in 12, 24, and 36 inch.

## Модели



### **Fluke i1730-flex6000**

A 36 inch Current Clamp

---

**Fluke.** *Keeping your world up and running.*®

ООО «Флюк СИИЭС»  
125993, г. Москва, Ленинградский  
проспект д. 37 к. 9 подъезд 4, 1 этаж,  
БЦ «Аэростар»  
Тел: +7 (495) 664-75-12  
Факс: +7 (495) 664-75-12  
e-mail: info@fluke.ru

© Авторское право 2021 Fluke Corporation.  
Авторские права защищены. Данные могут  
быть изменены без уведомления.  
Самые надежные инструменты в мире  
12/2021

**Не разрешается вносить изменения в данный  
документ без письменного согласия компании  
Fluke Corporation.**