

## i410 Токовые клещи



### Ключевые особенности

- Battery-powered Hall-effect probe measures 1A to 400 A
- 1mV/Amp output guarantees easy reading on your meter
- Take accurate current readings without breaking the circuit
- Maximum conductor Ø 32 mm
- CAT III 600 V safety rating
- Also available with softcase for DMM and clamp (i410 kit)
- One year warranty

### Обзор прибора: i410 Токовые клещи

The Fluke i410 AC/DC current clamp expands the functionality of digital multimeters and measures up to 400 amps for both AC and DC current. The Large clamp claw gives you access to difficult to reach areas. The kit includes a handy carrying case.

### Характеристики: i410 Токовые клещи

Specifications	
Measurement type	Hall sensor
Nominal current range	400 A, AC/DC

Continuous current range	1 A - 400 A AC/DC
Maximum non-destructive current	400 A
Lowest measureable current	0.5 A
Basic accuracy	3.5% + 0.5 A (% reading + floorspec)
Useable frequency	DC - 3 kHz
Output level(s)	1 mV/A
Zero error adjustment	Yes
<b>Safety Specifications</b>	
Safety	CAT III, 600 V
Maximum voltage	600 V
<b>Mechanical and General Specifications</b>	
Warranty	1 year
Battery life	9 V, 60 h
Maximum conductor diameter	30 mm 2 x 25 mm
Output cable length	1.6 m
Shrouded banana plugs	Yes

## Модели



### **i410**

Токоизмерительные клещи постоянного/переменного тока

---

**Fluke. Keeping your world up and running.®**

ООО "Флюк СИИЭС"  
125993, г. Москва, Ленинградский  
проспект д. 37 к. 9 подъезд 4, 1 этаж,  
БЦ «Аэростар»  
Тел: +7 (495) 664-75-12  
Факс: +7 (495) 664-75-12  
e-mail: info@fluke.ru

© Авторское право 2021 Fluke Corporation.  
Авторские права защищены. Данные могут  
быть изменены без уведомления.  
Самые надежные инструменты в мире  
12/2021

**Не разрешается вносить изменения в данный  
документ без письменного согласия компании  
Fluke Corporation.**