

Tekniska data


Fluke EI-1623 Selective/Stakeless Clamp Set



Produktöversikt: Fluke EI-1623 Selective/Stakeless Clamp Set

The Selective/Stakeless clamp set is used along with the Fluke 1623-2 and 1625-2 to perform Selective and Stakeless testing. Selective testing means using one clamp along with earth ground stakes to provide earth ground loop resistance values for one earth ground electrode. Stakeless testing uses both clamps provided to perform earth ground loop resistance measurement without stakes. Both tests have the advantage of providing measurements with no disconnection from the grounding system! Safer and quicker. Already included in the Fluke 1623-2 and 1625-2 kits. Both clamps have a 50.8 mm (2-inch) inner diameter.

Modeller



Fluke EI-1623

Fluke EI-1623 Selective/Stakeless Clamp Set

Fluke. *Keeping your world up and running.*®

Fluke Sverige AB
c/o Gilbarco Veeder-Root
Johannesfredsvägen 11 A
16869 Bromma
Tel: 08 5663 7400
E-mail: cs.se@fluke.com
www.fluke.se

©2021 Fluke Corporation. Med ensamrätt. Data kan komma att ändras utan föregående meddelande.
11/2021

Ändringar får inte göras i det här dokumentet utan skriftligt medgivande från Fluke Corporation.