

Tekniska data

Fluke i410-KIT AC/DC Current Clamp and Carry Case Kit



Produktöversikt: Fluke i410-KIT AC/DC Current Clamp and Carry Case Kit

Special value kit for electrical professional who is looking to add on DC and AC current measurement capabilities to their DMM. Includes a roomy carry case to hold and protect your meter and current clamp, plus extra storage for your test leads, probes and manuals.

Modeller



Fluke i410 Kit

- [i410](#) 1-400A AC rms, 1-400A DC Current Clamp
- Zippered vinyl carry case with moveable divider

Fluke. *Keeping your world up and running.*®

Fluke Sverige AB
c/o Gilbarco Veeder-Root
Johannesfredsvägen 11 A
16869 Bromma
Tel: 08 5663 7400
E-mail: cs.se@fluke.com
www.fluke.se

©2021 Fluke Corporation. Med ensamrätt. Data kan komma att ändras utan föregående meddelande. 12/2021

Ändringar får inte göras i det här dokumentet utan skriftligt medgivande från Fluke Corporation.