

Tekniska data

TL28A Autotestkabelset



Nyckelfunktioner

- Flexible silicone insulated leads are heat and cold resistant
- Cat I 30 V, 10 A

Produktöversikt: TL28A Autotestkabelset

Large jaws, long leads and a piercing needle inside the jaws. Solid, spring-loaded copper clips with a wide 12.7 mm (.50") jaw opening and serrated teeth. Large piercing needle for penetrating larger gauge wires located inside the jaws. 1.5 m (60"), silicone-insulated leads, useable from -80 °C to +70 °C (-112 °F to +158 °F). Rated for 30 V, 10 A. One red, one black.

Modeller



Fluke TL28A

Fluke. *Keeping your world up and running.*®

Fluke Sverige AB
c/o Gilbarco Veeder-Root
Johannesfredsvägen 11 A
16869 Bromma
Tel: 08 5663 7400
E-mail: cs.se@fluke.com
www.fluke.se

©2022 Fluke Corporation. Med ensamrätt. Data kan komma att ändras utan föregående meddelande.
01/2022

Ändringar får inte göras i det här dokumentet utan skriftligt medgivande från Fluke Corporation.