

ข้อมูลด้านเทคนิค

Fluke FOM Fiber Optic Meter



ภาพรวมผลิตภัณฑ์: Fluke FOM Fiber Optic Meter

The Fluke Fiber Optic Meter (FOM) helps you test and maintain fiber optic cable without having to buy a whole new meter. Plug the FOM directly into any DMM with a mV dc function and a 10 M Ω input impedance and quickly and accurately verify fiber optic cable system loss. Light sources and patch cords sold separately.

รุ่น**Fluke FOM**Fluke FOM Fiber Optic Meter

Fluke. ทั่วโลกของคุณ คงอยู่แค่ก้าวต่อไป

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/th-th

©2021 Fluke Corporation. Specifications subject to
change without notice.
12/2021

Modification of this document is not permitted without
written permission from Fluke Corporation.