


ข้อมูลด้านเทคนิค

Fluke BP290 2400 mAh High Capacity Li-Ion Battery for Fluke 190-Series-II



รุ่น



Fluke BP290

2400 mAh High Capacity Li-Ion Battery for Fluke 190-series II

Fluke. ให้โลกของคุณ คงอยู่แต่ละก้าวต่อไป

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/th-th

©2021 Fluke Corporation. Specifications subject to
change without notice.
12/2021

Modification of this document is not permitted without
written permission from Fluke Corporation.