

ข้อมูลด้านเทคนิค

## Fluke CXT80 Extreme Case



### คุณลักษณะสำคัญ

- Buoyancy allows case to float in salt water with 3.6 kg (7.94 lb) load
- Includes an automatic purge valve for quick equalization after changes in atmospheric pressure
- Features an exclusive 6.4 mm (0.25 in) neoprene O-ring and ABS latches for excellent seal

### ภาพรวมผลิตภัณฑ์: Fluke CXT80 Extreme Case

Unbreakable, watertight, airtight, dustproof, chemical resistant and corrosion proof.

รุ่น



### Fluke CXT80

For use with the following test tools:

- Multimeters: 27, 83 V, 85 V, 87 V, 187, 189
- Process Tools: 724, 725, 726, 789

## Fluke. ทั่วโลกของคุณ คงอยู่แค่ก้าวต่อไป

Fluke Corporation  
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:  
In the U.S.A. (800) 443-5853  
In Europe/M-East/Africa  
+31 (0)40 267 5100  
In Canada (800)-36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com/th-th](http://www.fluke.com/th-th)

©2021 Fluke Corporation. Specifications subject to  
change without notice.  
12/2021

Modification of this document is not permitted without  
written permission from Fluke Corporation.