

ข้อมูลด้านเทคนิค

Fluke i1730-flex1500/3pk iFlex® Current Clamps



ภาพรวมผลิตภัณฑ์: Fluke i1730-flex1500/3pk iFlex® Current Clamps

หัววัดกระแสไฟฟ้าแบบยืดหยุ่น iFlex ขนาด 12 นิ้ว ของเครื่องมือบันทึกพลังงาน Fluke 1730 ช่วยเพิ่มช่วงการตรวจวัดของ Fluke 1730 ได้ถึง 1500 A AC พร้อมกับให้ความยืดหยุ่นในการตรวจวัดที่สูงล้ำ หัววัด iFlex เชื่อมต่อโดยตรงเข้ากับเครื่องมือบันทึก ซึ่งจะแสดงการตรวจวัดกระแสไฟฟ้า โดยปราศจากปัจจัยด้านอัตราส่วนหัววัดที่ผิดพลาด สายไฟความยาว 1.8 ม. (6 ฟุต) ช่วยให้สามารถแยกตำแหน่งการตรวจวัดและเครื่องมือบันทึกออกจากกันได้ ทำให้การดูหน้าจอสถิติแสดงผลง่ายขึ้น สายเคเบิล iFlex ของเครื่องมือบันทึกพลังงาน Fluke 1730 มีอยู่ในรุ่นขนาด 12, 24 และ 36 นิ้ว

รุ่น

**Fluke i1730-flex1500/3pk**

1500A 12 inch, 3 Pack

- 1500A 12 inch, 3 pack iFlex® Current Clamps

Fluke. ทั่วโลกของคุณ คงอยู่แค่กระดาษต่อไป

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/th-th

©2021 Fluke Corporation. Specifications subject to
change without notice.
12/2021

Modification of this document is not permitted without
written permission from Fluke Corporation.