


ข้อมูลด้านเทคนิค

Fluke 71X Hose Kit Accessory



ภาพรวมผลิตภัณฑ์: Fluke 71X Hose Kit Accessory

The Fluke 71X Hose Kit is compatible with the 717 and 718 calibrators 100 PSI and below.

Application: Translucent accessory hoses allow the technician to easily identify if there is oil or other contaminants in the hose before they get into your calibrator.

Included: The kit contains three translucent hoses one meter long, easy to connect push fit connectors for both connection to the calibrator and the device under test, and one 1/8 to 1/4 NPT female-female adapter.

รุ่น

**Fluke 71X**

Hose Kit Accessory

Fluke. ให้โลกของคุณ คงอยู่แต่ละก้าวต่อไป

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/th-th

©2021 Fluke Corporation. Specifications subject to
change without notice.
11/2021

Modification of this document is not permitted without
written permission from Fluke Corporation.