

ข้อมูลด้านเทคนิค

## Fluke L200 Probe Light



### คุณลักษณะสำคัญ

- Small, rugged light easily attaches to any Fluke test probe
- Bright white LED illuminates contact area
- Frees both hands for work
- 120 hours of battery life
- Uses 2 3-volt watch batteries

รุ่น



**Fluke L200**

---

**Fluke. ให้โลกของคุณ คงอยู่แต่ละก้าวต่อไป**

Fluke Corporation  
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:  
In the U.S.A. (800) 443-5853  
In Europe/M-East/Africa  
+31 (0)40 267 5100  
In Canada (800)-36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com/th-th](http://www.fluke.com/th-th)

©2021 Fluke Corporation. Specifications subject to  
change without notice.  
12/2021

Modification of this document is not permitted without  
written permission from Fluke Corporation.