

ข้อมูลด้านเทคนิค

Fluke 80K-40 High Voltage Probe



คุณลักษณะสำคัญ

- A high voltage probe that allows a multimeter to measure up to 40,000V respectively. Intended for low energy applications only
- One year warranty

ภาพรวมผลิตภัณฑ์: Fluke 80K-40 High Voltage Probe

The 80K-40 is a high voltage probe designed to extend the voltage measuring capability of an AC/DC voltmeter to 40,000 volts peak AC or DC Overvoltage Category I. This means the probe can only be used to make measurements on energy limited circuits within equipment. Examples include high voltage within televisions or photo copy machines. DO NOT use this probe to measure high voltages on power distribution systems. The probe provides high accuracy when used with a voltmeter having 10 Megohm input impedance.

รุ่น



Fluke 80K 40

Fluke. ทั่วโลกของคุณ คงอยู่แค่ก้าวต่อไป

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/th-th

©2021 Fluke Corporation. Specifications subject to
change without notice.
12/2021

Modification of this document is not permitted without
written permission from Fluke Corporation.