

Fluke 85RF High Frequency Probe



ภาพรวมผลิตภัณฑ์: Fluke 85RF High Frequency Probe

The 85RF High Frequency Probe is designed to convert a DC voltmeter with a input impedance of 10M ohms into a high frequency (100 kHz to 500 Mhz) RF voltmeter. Conversion from AC to DC is accomplished on a one-to-one basis includes a range of 0.25 to 30 Vrms. The probe's DC output is calibrated to be equivalent to the rms value of a sine wave input.

ข้อมูลจำเพาะ: Fluke 85RF High Frequency Probe

Specifications	
Voltage range	0.25 to 30 Vrms
Maximum input voltage	30 Vrms, 200 VDC
AC to DC ratio	1:1
Ratio Accuracy (At 25 MHz and loaded with 10 M ohm) Above 0.5 V	±0.5 dB
	Below 0.5 V: ±1.0 dB
	Add ±0.2 dB in RF fields of 1 to 3 V/m
Frequency response (relative to 25 MHz)	100 KHz to 100 MHz ±0.5 dB
	100 MHz to 200 MHz ±2.0 dB
	200 MHz to 500 MHz ±3.0 dB

รุ่น



Fluke 85RF

Fluke. ให้โลกของคุณ คงอยู่แต่ละก้าวต่อไป

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Europe/M-East/Africa
+31 (0)40 267 5100
In Canada (800)-36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com/th-th

©2021 Fluke Corporation. Specifications subject to
change without notice.
12/2021

Modification of this document is not permitted without
written permission from Fluke Corporation.